



FD42GN

Enclosure, NewVegaD, 750x550x193mm, 96 modules, surface-mounted, empty

Technical properties

Configuration

Number of modules	96
-------------------	----

Electric current

Rated current	160 A
---------------	-------

Dimensions

Depth of installed product	193 mm
Internal depth	193 mm
Height of installed product	750 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	1 mm

Cover, door

Cover type	With Notch
Door leave	without
Cover type	none / closed
Transparent cover or door	No

Materials

Colour	white
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	4
Quantity of rails	0
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	No

Standards

Subject to technical modifications

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-