



FD52DN

**Enclosure, NewVegaD, 900x550x193mm, 120 modules, surface-mounted, distribution**

**Technical properties**

**Configuration**

Module	with terminals
Number of modules	120

**Main electrical features**

Nominal voltage	230/400 V
-----------------	-----------

**Electric current**

Rated current	160 A
---------------	-------

**Dimensions**

Depth of installed product	193 mm
Internal depth	189 mm
Height of installed product	900 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	2 mm

**Cover, door**

Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	none / closed
Transparent cover or door	No

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	4
--------------------------	---

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	5
Quantity of rails	5
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No

### **Safety**

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No