



FD62DN

**Enclosure, NewVegaD, 1050x550x193mm, 144 modules, surface-mounted, distribution**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Configuration**

Number of modules 144

**Electric current**

Rated current 160 A

**Dimensions**

Depth of installed product 193 mm

Internal depth 189 mm

Height of installed product 1050 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 2 mm

**Cover, door**

Number of keylock of the door 0

Cover type With Notch

Door locking without

Door leave single

Cover type none / closed

Transparent cover or door No

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

**Installation, mounting**

Suitable for outdoor use No

**Connection**

Number of conduit inlets 4

**Settings**

Enclosure type Distributor empty cabinet

**Equipment**

Number of rows 6

Quantity of rails	6
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP30
Protection class	isol.class II