



FU42AN

Enclosure, NewVegaD, 837x550x182mm, 96 modules, flush-mounted, to complete

Technical properties

Configuration

Module	with terminals
Number of modules	96

Electric current

Rated current	160 A
---------------	-------

Dimensions

Insertion depth	110 mm
Depth of installed product	182 mm
Internal depth	110 mm
Height of installed product	837 mm
Installation height	837 mm
Width of installed product	600 mm
Width in division units	24
Thickness of sidewall material	1 mm
Built-in width	550 mm

Cover, door

Cover type	With Notch
Door locking	without
Door leave	single
Cover type	none / closed
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	4
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	4
----------------	---

Quantity of section in width	2
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No