



FU72AN

Enclosure, NewVegaD, 1287x550x182mm, 168 modules, flush-mounted, to complete

Technical properties

Configuration

| | |
|-------------------|----------------|
| Module | with terminals |
| Number of modules | 168 |

Electric current

| | |
|---------------|-------|
| Rated current | 160 A |
|---------------|-------|

Dimensions

| | |
|--------------------------------|---------|
| Insertion depth | 110 mm |
| Depth of installed product | 182 mm |
| Internal depth | 110 mm |
| Height of installed product | 1287 mm |
| Installation height | 1287 mm |
| Width of installed product | 600 mm |
| Width in division units | 24 |
| Thickness of sidewall material | 1 mm |
| Built-in width | 550 mm |

Cover, door

| | |
|---------------------------|---------------|
| Cover type | With Notch |
| Door locking | without |
| Door leave | single |
| Cover type | none / closed |
| Transparent cover or door | No |

Materials

| | |
|---------------------------|-----------------------|
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Type of surface treatment | powder-coated |

Installation, mounting

| | |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

Connection

| | |
|--------------------------|---|
| Number of conduit inlets | 4 |
|--------------------------|---|

Settings

| | |
|----------------|---------------------------|
| Enclosure type | Distributor empty cabinet |
|----------------|---------------------------|

Equipment

| | |
|----------------|---|
| Number of rows | 7 |
|----------------|---|

| | |
|--------------------------------------|-----|
| Quantity of section in width | 2 |
| Quantity of rails | 5 |
| Can be accessorized | Yes |
| Number of openings for flange plates | 2 |
| Extension possible | No |
| Earthing terminal block | No |
| Neutral terminal block | No |
| Signal passing door | No |

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|------------------|---------------|
| Protection class | isol.class II |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |