



FU72AN

**Enclosure, NewVegaD, 1287x550x182mm, 168 modules, flush-mounted, to complete**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Configuration**

Module with terminals

Number of modules 168

**Electric current**

Rated current 160 A

**Dimensions**

Insertion depth 110 mm

Depth of installed product 182 mm

Internal depth 110 mm

Height of installed product 1287 mm

Installation height 1287 mm

Width of installed product 600 mm

Width in division units 24

Thickness of sidewall material 1 mm

Built-in width 550 mm

**Cover, door**

Cover type With Notch

Door locking without

Door leave single

Cover type none / closed

Transparent cover or door No

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

**Installation, mounting**

Suitable for outdoor use No

**Connection**

Number of conduit inlets 4

**Settings**

Enclosure type Distributor empty cabinet

**Equipment**

Number of rows	7
Quantity of section in width	2
Quantity of rails	5
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	No

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No