



HA780120

**slotted panel trunking HA7 80x120, light grey**

**Technical properties**

**Architecture**

Flexible No

**Configuration**

Side wall configuration Slotted

**Electric current**

Current leak stable Yes

**Dimensions**

Trunking height 80 mm

Length 2000 mm

Trunking width 120 mm

Slot width 6 mm

Tongue width 6.5 mm

**Cover, door**

Lid shape loose

**Materials**

RAL colour RAL 7035 - Light grey

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching EN 50085-2-3:1999

Fixing type bottom punching

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 315

Internal/useful cross section 7898 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 226

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 438

**Standards**

Approvals EN50085-2-3

European directive RoHS voluntary compliance

UL 94 classification V0

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Fireproof classification	M1

**temperatur**

---

Ambient temperature	-25...90 °C
---------------------	-------------