



HXF042H

Motor operator H1250-H1600 200-230VAC

Technical properties

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Rated operational voltage Ue	200 / 230 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

DC control voltage	0 V
Command voltage AC	200 / 230 V
Rated operational voltage in DC	0 V

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	24 W
---------------------------	------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m