



HXF042H

Motor operator H1250-H1600 200-230VAC

Technical properties

Architecture

Type of order motor drive

Main electrical features

Rated operational voltage Ue 200 / 230 V

Type of supply voltage AC

Frequency 50/60 Hz

Voltage

DC control voltage 0 V

Command voltage AC 200 / 230 V

Rated operational voltage in DC 0 V

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under IN 24 W

Standards

European directive RoHS voluntary compliance

European directive WEEE concerned

Safety

Protection index IP IP4X

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m