



HYC003H

### Collar terminal H250 Cu 3P

#### Technical properties

##### Architecture

Number of poles 3 P

##### Electric current

Rated current 250 A

##### Installation, mounting

Tightening torque 19Nm

##### Connection

Connection cross-sect. flexible conductor 35 / 120mm<sup>2</sup>

Connection cross-sect. rigid cable 35 / 120mm<sup>2</sup>

##### Cable

Cable Material Cu

##### Standards

European directive WEEE concerned

##### Safety

Protection index IP IP4X

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m