



KDN180B

Insulated busbar 1P 80A fork 16mm² 57M

Technical properties

Architecture

Number of poles	1 P
-----------------	-----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
-----------------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Length	1000 mm
--------	---------

Pitch	17.8 mm
-------	---------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	16mm ²
------------------------------------	-------------------

Suitable for product with neutral busbar	No
--	----

Equipment

Number of appliances to build in	57
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Use conditions

Insulated	Yes
-----------	-----