



L2212



Flexible slotted panel trunking halogenfree 10mm Länge = 250mm light grey

Technical properties

Architecture

Flexible Yes

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 10 mm

Length 250 mm

Trunking width 10 mm

Slot width 8 mm

Tongue width 4.5 mm

Cover, door

Lid shape none

Materials

Colour light grey

Material Polyamid (PA)

Material group plastic

Type of surface treatment untreated

Installation, mounting

Fixing type selfadhesive and bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 8

Internal/useful cross section 100 mm²

Number of wires 2,5 mm² - 40% filling degree 5

Number of wires 1,0 mm² - 40% filling degree 10

Standards

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

| | |
|---------------------|-------------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| temperatur | |
| Ambient temperature | -25...90 °C |