



LS601



**Fuse carrier 1P 50A 690V L51 accessoriability 1.5M**

**Technical properties**

**Architecture**

Number of poles	1 P
Type of pole	1 P

**Configuration**

Number of modules	1.5
-------------------	-----

**Electric current**

Rated current	50 A
---------------	------

**Fuse**

CharactFuse	gG ; aM
-------------	---------

**Dimensions**

Depth of installed product	93 mm
Height of installed product	107 mm
Width of installed product	26.25 mm

**Power**

Total power loss under IN	6.098 W
---------------------------	---------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C