



M5693



Flexible slotted panel trunking Polyamid halogenfree 40mm Länge=0,5m light grey

Technical properties

Architecture

Flexible Yes

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Length 500 mm

Slot width 8 mm

Tongue width 4.5 mm

Cover, door

Lid shape none

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching With base punching

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 81

Internal/useful cross section 620 mm²

Number of wires 2,5 mm² - 40% filling degree 53

Number of wires 1,0 mm² - 40% filling degree 101

Standards

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

