



SP120

## SPD 1P monobloc 50kA class 1

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

Indicator lamp	no
----------------	----

#### Main electrical features

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	50 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	36 mm
----------------------------	-------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Network configuration

Network type	TT/TN
--------------	-------

#### Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	35mm <sup>2</sup>
Connection cross-sect. rigid cable	50mm <sup>2</sup> max.

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T1
European directive WEEE	concerned

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-40...80 °C
Storage/transport temperature	-40...80 °C