



SPN800

SPD 3P pluggable 75kA class 1 with end of life indicator TNC

Technical properties

Configuration

Number of modules 6

Controls and indicators

Indicator lamp end of life indicator

Main electrical features

Test class type1 IEC61643-11 Yes

Frequency 50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 75 kA

Dimensions

Depth of installed product 83 mm

Width of installed product 108 mm

Power

Total power loss under IN 0 W

Network configuration

Network type TN-C

Installation, mounting

Tightening torque 3,6Nm

Connection

Connection cross-sect. flexible conductor 35mm²

Connection cross-sect. rigid cable 35mm²

Standards

Test class IEC61643-11 / VDE0675-6-11 T1

Use conditions

Operating temperature -40...60 °C

Storage/transport temperature -40...80 °C