



SPN800

SPD 3P pluggable 75kA class 1 with end of life indicator TNC

Technical properties

Configuration

Number of modules	6
-------------------	---

Main electrical features

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	75 kA
-------------------------------------	-------

Dimensions

Depth of installed product	83 mm
Width of installed product	108 mm

Power

Total power loss under IN	0 W
---------------------------	-----

Network configuration

Network type	TN-C
--------------	------

Standards

Test class IEC61643-11 / VDE0675-6-11	T1
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-40...60 °C
Storage/transport temperature	-40...80 °C