



SPN802

SPD 4P pluggable 100kA class 1 with end of life indicator TT

Technical properties

Configuration

Number of modules	8
-------------------	---

Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

Main electrical features

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	100 kA
-------------------------------------	--------

Dimensions

Depth of installed product	83 mm
Width of installed product	144 mm

Power

Total power loss under IN	0 W
---------------------------	-----

Network configuration

Network type	TT
--------------	----

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	35mm ²
Connection cross-sect. rigid cable	35mm ²

Standards

Test class IEC61643-11 / VDE0675-6-11	T1
---------------------------------------	----

Use conditions

Operating temperature	-40...60 °C
Storage/transport temperature	-40...80 °C