

24V +/- 5%

72 mm

15 W



TGA200































































Power supply 24 V DC 1A

Technical properties

Architecture

Bus system EIB

Configuration

Number of modules 4

Main electrical features

Frequency 50/60 Hz

Voltage

Output voltage 24 V DC
Output voltage 24 V

Electric current

Filtered output voltage

Output current 1 A

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Width of installed product

Power

Current consumption150 mAPower consumed16 VAPower consumption (standby)0.2 W

Total power loss under IN

Measurement

Voltage measurement range 22.8 to 25.2 V

Materials

RAL colour RAL 7035 - Light grey

Installation, mounting

Modular version Yes
Suitable for front mounting No

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of connection	with QuickConnect plug-in terminals
Type of connection	Quickconnect
Equipment	
Equipment	
Short-circuit protected	Yes
Use	
Differentiation characteristic 1 - Sales	with labelling field
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No