



TGA200



## Power supply 24 V DC 1A

### Technical properties

#### Architecture

Bus system	EIB
------------	-----

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Output voltage	24 V DC
----------------	---------

Output voltage	24 V
----------------	------

Filtered output voltage	24V +/- 5%
-------------------------	------------

#### Electric current

Output current	1 A
----------------	-----

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Width of installed product	72 mm
----------------------------	-------

#### Power

Current consumption	150 mA
---------------------	--------

Power consumed	16 VA
----------------	-------

Power consumption (standby)	0.2 W
-----------------------------	-------

Total power loss under IN	15 W
---------------------------	------

#### Measurement

Voltage measurement range	22.8 to 25.2 V
---------------------------	----------------

#### Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

#### Installation, mounting

Modular version	Yes
-----------------	-----

Suitable for front mounting	No
-----------------------------	----

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
------------------------------------	---------------------------

Type of connection	with QuickConnect plug-in terminals
Type of connection	Quickconnect
<b>Equipment</b>	
Short-circuit protected	Yes
<b>Use</b>	
Differentiation characteristic 1 - Sales	with labelling field
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No