



TJA450

domovea Softwarelösung (Server + Client) mit USB/KNX Interface

Technical properties

Architecture

Fixing mode	REG
-------------	-----

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Electric current

Current consumption (operation)	≈ 150 mA
---------------------------------	----------

Power

Total power loss under IN	3.9 W
---------------------------	-------

Storage

Memory allocated to the icons/wallpapers	20 MB
--	-------

Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey
Material	plastic
Type of surface treatment	untreated

Connection

Number of IP cameras	10
Type of connection	Quickconnect

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Accessories included

Accessory for Android application	Yes
Accessory for IOS application	yes

Equipment

Number of group	100
Number of controllable outputs	500
Number of clients	30

Number of energie measurement archives	100
Number of sequences	50
Number of USB interfaces	3
With configuration software	Yes
Software	
Client software	Yes
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	0...45 °C
Identification	
Main design line	KNX