



TJA450

domovea Softwarelösung (Server + Client) mit USB/KNX Interface

Technical properties

Architecture

Fixing mode REG

Configuration

Number of modules 6

Controls and indicators

Indicator lamp yes

Electric current

Current consumption (operation) ≈ 150 mA

Power

Total power loss under IN 3.9 W

Storage

Memory allocated to the icons/wallpapers 20 MB

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Material other

Material plastic

Type of surface treatment untreated

Connection

Number of IP cameras 10

Type of connection Quickconnect

Settings

Supported configuration modes system

Scope of delivery

Bus connection included Yes

Accessories included

Accessory for Android application Yes

Accessory for IOS application yes

Equipment

Number of group 100

Number of controllable outputs 500

Number of clients	30
Number of energie measurement archives	100
Number of sequences	50
Number of USB interfaces	3
With configuration software	Yes
Software	
Client software	Yes
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	0...45 °C
Identification	
Main design line	KNX