



TXA111



**Power supply 30V DC 320 mA**

### Technical properties

#### Architecture

Fixing mode Din-Rail

#### Configuration

Number of modules 4

#### Connectivity

Bus lines 1

#### Main electrical features

Frequency 50/60 Hz

#### Voltage

Output voltage 28...32 V

Filtered output voltage 30V +/- 2V

#### Electric current

Output current max. 320 mA

Output intensity 320 mA

#### Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

#### Power

Total power loss under IN 15 W

#### Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

#### Connection

Conductor cross-section (flexible) 0.75...2.5 mm<sup>2</sup>

Conductor cross-section (rigid) 0.75...2.5 mm<sup>2</sup>

#### Use

Differentiation characteristic 1 - Sales with labelling field

#### Safety

Protection index IP IP20

**Use conditions**

---

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

---