



TXA208B

8-fold output module 10A/230V~ with manual override without bus supply

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	230 V
Rated current	10 A

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Electric current

Number of entry circuits	0
Maximum through current	10 A
Rated current	10 A

Power

Max. power with electronic transfo.	1000 W
Total power loss under IN	6 W
Output power	1200 W
Max. switching power	7200 W

Materials

Colour	stone grey
--------	------------

Incandescent bulbs control

Max. power with incandescent lamps	1200 W
------------------------------------	--------

Connection

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment	
Number of outputs	8
Bidirectional radio frequency	No
Modular expandability	No
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX