



TXA210N

## Dimmer 1 channel 600W

### Technical properties

#### Architecture

Bus system KNX

#### Configuration

Number of modules 4

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Frequency 50/60 Hz

Rated current 2.6 A

#### Voltage

System supply voltage 30V DC via bus

#### Power

Incandescent bulb power 20 / 600 W

Total power loss under IN 4.8 W

Power of the variator 0 / 600 W

#### Fluorescent bulbs control

Power lighting fluo lamps 120W

#### LED control

Power LED 120 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of load universal

Type of connection quick connect

#### Equipment

Type of dimmer universal

Bidirectional radio frequency No

#### Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C