



TXA213N

Dimmer 3 channels 300W

Technical properties

Architecture

Bus system KNX

Configuration

Number of modules 6

Controls and indicators

Indicator lamp yes

Main electrical features

Frequency 50/60 Hz

Rated current 3.9 A

Voltage

System supply voltage 30V DC via bus

Power

Incandescent bulb power 20 / 900 W

Total power loss under IN 5.8 W

Power of the variator 0 / 900 W

Fluorescent bulbs control

Power lighting fluo lamps 3x60W/1x60W+1x12W/1x210W

LED control

Max number of LED/CFL lamps 15

Power LED 210 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of load universal

Type of connection quick connect

Equipment

Type of dimmer universal

Bidirectional radio frequency No

Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C