



TXA224

Output device for 4 shutters or blinds 230V~

Technical properties

Architecture

Bus system	KNX
Number of blinds/shutters outputs	4

Functions

Bus module detachable	No
-----------------------	----

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

System supply voltage	30V DC via bus
-----------------------	----------------

Electric current

Number of entry circuits	0
Maximum switching current	6 A

Power

Contact rating with 230 V in AC1	1380 W
Total power loss under IN	2 W

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Number of contacts	4
Type of connection	quick connect

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Bidirectional radio frequency	No
-------------------------------	----

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C

