



TXA226

## Output device for 4 shutters / blinds 24V DC

### Technical properties

#### Architecture

Bus system	EIB
Number of blinds/shutters outputs	4

#### Functions

Bus module detachable	No
-----------------------	----

#### Configuration

Number of modules	4
-------------------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Type of supply voltage	DC
------------------------	----

#### Voltage

System supply voltage	30V DC via bus
-----------------------	----------------

#### Electric current

Number of entry circuits	0
Maximum switching current	6 A

#### Power

Contact rating with 230 V in AC1	1380 W
Total power loss under IN	2 W

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2,5mm <sup>2</sup>
Number of contacts	4
Type of connection	quick connect

#### Scope of delivery

Bus connection included	Yes
-------------------------	-----

#### Equipment

Bidirectional radio frequency	No
-------------------------------	----

#### Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C

