



VF418PZF

Small distributor,golf,flush,MM,72M,4row,white door,slotted

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	72
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	688 mm
Installation height	652 mm
Width of installed product	460 mm
Width in division units	18
Built-in width	426 mm

Cover, door

Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
Equipment	
Number of units	18
Number of rows	4
Quantity of rails	4
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes
Standards	
GWT Glow wire test	650 °C
European directive WEEE	not concerned
Safety	
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No