



VS104PF

**Small distributor,golf,surface,1row,IP40,4M,MS-terminal,PE,white door**

## Technical properties

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Functions

With a pipe-in lead	Yes
---------------------	-----

### Configuration

Number of modules	4
-------------------	---

### Main electrical features

Nominal voltage	400 V
-----------------	-------

### Electric current

Rated current	63 A
---------------	------

### Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	184 mm
Width of installed product	138 mm
Width in division units	4

### Cover, door

Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes

**Standards**

GWT Glow wire test	650 °C
European directive WEEE	not concerned

**Safety**

Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------