



WXA010

## Lamp gallery for plate 1P 230V pure-white

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Electric current

Rated current	2.5 mA
---------------	--------

#### Dimensions

Depth	6.9 mm
Height	39.4 mm
Width	87.8 mm

#### Power

Current consumption	max. 2.5 mA
---------------------	-------------

#### Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

#### Lighting control

Light colour	white
Type of lamp	LED

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	NF
European directive RoHs	voluntary compliance

#### Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range

gallery

Composition

other