



WXA011

Lamp gallery for plate 1P 12/24V pure-white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Main electrical features

Nominal voltage	24 V
-----------------	------

Electric current

Rated current	7.5 mA
---------------	--------

Dimensions

Depth	6.9 mm
Height	39.4 mm
Width	87.8 mm

Power

Current consumption	max. 7.5 mA
---------------------	-------------

Materials

Colour	transparent
RAL colour	RAL 9010 - Pure white

Lighting control

Light colour	white
Type of lamp	LED

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NF
European directive RoHS	voluntary compliance
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

