



WXA011

### Lamp gallery for plate 1P 12/24V pure-white

#### Technical properties

##### Architecture

Fixing mode Clipped

##### Main electrical features

Nominal voltage 24 V

##### Electric current

Rated current 7.5 mA

##### Dimensions

Depth 6.9 mm

Height 39.4 mm

Width 87.8 mm

##### Power

Current consumption max. 7.5 mA

##### Materials

Colour transparent

RAL colour RAL 9010 - Pure white

##### Lighting control

Light colour white

Type of lamp LED

##### Equipment

With transparent product label holder No

##### Standards

European directive RoHS voluntary compliance

European directive WEEE concerned

##### Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

##### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

##### Identification

Range

gallery

Composition

other