



WXA450

Frame gallery 2 modules

Technical properties

Dimensions

Depth	8.7 mm
Height	73.8 mm
Width	73.8 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Surface appearance	matt
Type of surface treatment	untreated

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NF
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	basis element