


WXA450G



Frame gallery 2 modules with claws

Technical properties

Dimensions

| | |
|--------|---------|
| Depth | 26.7 mm |
| Height | 73.8 mm |
| Width | 73.8 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|---------------------------|-----------|
| Surface appearance | matt |
| Type of surface treatment | untreated |

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-----------|----|
| Approvals | NF |
|-----------|----|

Safety

| | |
|---|-----|
| IK protection code against mechanical impacts | 05 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|---------------|
| Range | gallery |
| Composition | basis element |