



WXD253N

Rocker for TV+FM socket gallery 2 modules night

Technical properties

Architecture

Fixing mode Clipped

Connectivity

Outlet with straight outlet

Dimensions

Depth 8.4 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name night

Surface appearance satin finish

Equipment

Supporting plate / Supporting ring without supporting ring

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other