



WXF005

2 way switch gallery pull cord 2 modules

Technical properties

Architecture

Type of control unit	pull cord
Fixing mode	Clipped

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth	40.35 mm
Insertion depth	41 mm
Height	45 mm
Width	45 mm

Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	05
---	----

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C