



WXF005

**2 way switch gallery pull cord 2 modules**

**Technical properties**

**Architecture**

Type of order	Switch
Type of control unit	pull cord
Fixing mode	Clipped

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth	40.35 mm
Insertion depth	41 mm
Height	45 mm
Width	45 mm

**Materials**

Surface appearance	matt
Type of surface treatment	untreated

**Connection**

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	05
---	----

**Use conditions**

---

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

---

**Identification**

---

Range	gallery
Composition	Middle plate

---