



WXF160N

Schuko socket gallery 2P+E night

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	40.25 mm
Height	45 mm
Width	45 mm

Cover, door

Cover	Complete housing
-------	------------------

Materials

Free area for finishing name	night
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	Polycarbonate (PC)
Surface appearance	satın finish
Type of surface treatment	Painted
Metallic colour	No

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	VDE
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------