



WXF225

RJ45 socket gallery cat.6 UTP

Technical properties

Architecture

Type	UTP
------	-----

Connectivity

Outlet	with straight outlet
--------	----------------------

Dimensions

Depth	34.6 mm
Height	45 mm
Width	45 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Surface appearance	matt
--------------------	------

Connection

Connection cross-sect. rigid cable	0,5 - 0,65 mm ²
Connector type	shielding connection via Clip

Cable

AWG range	AWG 26-22
-----------	-----------

Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes
Protection	with optional dust protection hinged covers

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Application, usage	Communication technology
Range	gallery
Composition	Middle plate