



WXF254

**TV + FM socket gallery passthrough BNC socket 10 db 2 modules**

**Technical properties**

**Connectivity**

Passband	4 - 862 MHz
----------	-------------

**Dimensions**

Depth	34 mm
Height	45 mm
Width	45 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Surface appearance	matt
Type of surface treatment	untreated

**Safety**

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
Composition	Middle plate