



WXF300

Switch for shutter gallery 1 way 2 modules

Technical properties

Architecture

Type of order	Switch
Type of control unit	double rocker
Fixing mode	Clipped

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth	34 mm
Height	45 mm
Width	45 mm

Materials

Surface appearance	matt
Type of surface treatment	untreated

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 2,5mm ²
Type of connection	Quickconnect

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Middle plate
