



WXF300

## Switch for shutter gallery 1 way 2 modules

### Technical properties

#### Architecture

Type of order	Switch
Type of control unit	double rocker
Fixing mode	Clipped

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Depth	34 mm
Height	45 mm
Width	45 mm

#### Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

#### Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	EN 60669-1
European directive WEEE	concerned

#### Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
<b>Use conditions</b>	
Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
<b>Identification</b>	
Range	gallery
Composition	Middle plate