



WXF601

**Indicator gallery red et green 2 modules**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Main electrical features**

Nominal voltage	250 V
-----------------	-------

**Dimensions**

Depth	41.2 mm
Height	45 mm
Width	45 mm

**Power**

Max. power per charging point	1.4 W
-------------------------------	-------

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Surface appearance	glossy
Type of surface treatment	untreated

**Lighting control**

Type of lamp	LED
--------------	-----

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
Composition	Mechanism with upper casing