



WXF601

## Indicator gallery red et green 2 modules

### Technical properties

#### Architecture

Fixing mode Clipped

#### Main electrical features

Nominal voltage 250 V

#### Dimensions

Depth 41.2 mm

Height 45 mm

Width 45 mm

#### Power

Max. power per charging point 1.4 W

#### Capacity

Number of sockets 1

#### Materials

Colour dark grey

RAL colour RAL 7011 - Iron grey

Material Plastic/metal

Type of surface treatment untreated

#### Lighting control

Type of lamp LED

#### Standards

European directive WEEE concerned

#### Safety

IK protection code against mechanical impacts 05

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Mechanism with upper casing