



WXF622

Jack socket gallery audio keystone

Technical properties

Architecture

| | |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

Connectivity

| | |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

Dimensions

| | |
|--------|---------|
| Depth | 32.5 mm |
| Height | 45 mm |
| Width | 45 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|---------------------------|---------------|
| Material | Plastic/metal |
| Surface appearance | matt |
| Type of surface treatment | untreated |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK02 |
| Protection index IP | IP20 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|--------------|
| Range | gallery |
| Composition | Middle plate |