



WXF641

## SUB-D15 (VGA+minijack) gallery screw ter

### Technical properties

#### Connectivity

Outlet with straight outlet

#### Dimensions

Depth 34.7 mm

Height 45 mm

Width 45 mm

#### Capacity

Number of sockets 1

#### Materials

Surface appearance matt

Type of surface treatment untreated

#### Equipment

Supporting plate / Supporting ring without supporting ring

#### Safety

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Middle plate