



WXF688N

Blank function gallery 1 module night

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Dimensions

| | |
|-------|---------|
| Depth | 29.5 mm |
|-------|---------|

| | |
|--------|-------|
| Height | 45 mm |
|--------|-------|

| | |
|-------|---------|
| Width | 22.5 mm |
|-------|---------|

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|------------------------------|-------|
| Free area for finishing name | night |
|------------------------------|-------|

| | |
|--------------------|--------------|
| Surface appearance | satin finish |
|--------------------|--------------|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK02 |
|---|------|

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...35 °C |
|-----------------------|-------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -10...50 °C |
|-------------------------------|-------------|

Identification

| | |
|-------|---------|
| Range | gallery |
|-------|---------|

| | |
|-------------|-------|
| Composition | other |
|-------------|-------|

| | |
|--------------|----|
| With imprint | No |
|--------------|----|