



WXF689B

**Blank function gallery 2 modules pure-white**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	24 mm
Height	45 mm
Width	45 mm

**Capacity**

Number of sockets	3
-------------------	---

**Materials**

Free area for finishing name	pure
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
Composition	other
With imprint	No