



WXF689N

## Blank function gallery 2 modules night

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	24 mm
-------	-------

Height	45 mm
--------	-------

Width	45 mm
-------	-------

#### Capacity

Number of sockets	3
-------------------	---

#### Materials

Free area for finishing name	night
------------------------------	-------

Colour	deep black
--------	------------

RAL colour	RAL 9005 - Jet black
------------	----------------------

Type of surface treatment	Painted
---------------------------	---------

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	IK02
---	------

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

#### Identification

Range	gallery
-------	---------

Composition	other
-------------	-------

With imprint	No
--------------	----